

**Technical data**

Operating temperature range	-40...100 °C
Material	EPDM
Braiding	Yes
Nominal width (DN)	12 mm
Length	variable
Net weight	0,28 kg
Outer covering	without isolation
Outside diameter	19,6 mm
Max. pressure at 20°C	20 bar
Min. bending radius	50 mm

**Order-No.: 10506****1.0/16**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Information: Operation at high temperatures and/or high pressures should be limited to 12h/day to extend hose life.

When used with DW-Therm® these hoses may show deterioration earlier than when used with other recommend HUBER heat transfer fluids.