

Hydraulically sealed Refrigerated Heating Circulator with water-cooled refrigerating unit. Evaporator and housing made of stainless steel. With atmospheric open expansion tank and optical level indicator. As well as for externally closed and also externally open applications.

High system performance (watt/litre) due to minimized internal volume. No HTF vapour and no moisture absorption because the expansion tank is thermally passive. For external open baths the expansion tank will be blocked off. This means that the thermostat is atmospherically sealed and can be located below or above the level of the application. Powerful variable speed pump (soft start) with integrated pressure control with optional external pressure sensor.

#### Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

#### Further functions:

E-grade Professional installed as standard, TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 10 programs (max. 100 steps), ramp function (linear and non-linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K, integrated technical glossary, 2nd set point, user menus (Administrator level), calendar start, wallpaper selection.

4-year warranty - registration required.

#### Technical data according to DIN 12876

Operating temperature range	-45...250 °C	
Temperature stability at -10°C	0,01 K	
temperature set point / display	5,7" colour Touchscreen	<b>Order-No.: 1066.0020.01</b>
Resolution of display	0,01 K	
Internal temperature sensor	Pt100	
Sensor external connection	Pt100	
Interface digital	Ethernet, USB (Host u. Device), RS232	
digital input	ECS ONE	
digital output	POKO ONE	
Alarm message	optic, acoustic, relay	
Safety classification	III / FL	
Heating power	3 kW	
Cooling power with	Thermooil	
at 250°C	1,3 kW	
at 200°C	1,5 kW	
at 100°C	2,5 kW	
at 20°C	2,5 kW	
Cooling power with	Ethanol	
at 0°C	1,5 kW	
at -20°C	0,8 kW	
at -40°C	0,17 kW	
Refrigeration machine	water-cooled, natural refrigerant	
Refrigerant (ASHRAE, GHS)	R-1270 (A3, H220)	
Global Warming Potential (GWP)	0	
Circulation pump:		
max. delivery	56 l/min	
max. delivery pressure	0,9 bar	
Delivery at 0,2 bar	50 l/min	
Delivery at 0,4 bar	42 l/min	
Delivery at 0,6 bar	33 l/min	
Delivery at 0,8 bar	20 l/min	

## Technical data according to DIN 12876

---

Pump connection	M24x1,5 male
max. permissible kin. viscosity	50 mm <sup>2</sup> /s
Cooling water connection	G1/2 male
Consumption at water 15°C, flow 20°C	280 l/h
min. cooling water differential pressure	1 bar
max. cooling water pressure	6 bar
min. filling capacity	1,5 l
Filling capacity expansion tank	2,8 l
Overall dimensions WxDxH **	426x360x631 mm
Net weight	68 kg
sound pressure level +/- 4 dB(A)	61 dB(A)
Power supply requirement	220-240V 1~/2~ 50/60Hz
Pressure equipment category	Art. 4.3 PED
Degree of Protection	IP20
min. ambient temperature	5 °C
max. ambient temperature	40 °C

---

from Serial-No.:

1.0/23

---

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

mini-USB cable #54949, E-grade "Professional" #9496, Adaptor M16x1 male to M24x1,5 female, hose connection for G1/2 male

Optional accessories:

E-grade "Explore" #10495, RS232 adapter cable #55018, SpyLight-Software, Com.G@te Namur, PC-Com.G@te-cable, Holder for Com.G@te #10019; Com.G@te-extension cable: upon request, Thermofluid, external pressure sensor, metal hoses M16x1 or M24x1,5, braided hoses for cooling water, external sensor, connecting cable, isolation sleeve for external open applications, float switch in sight glass for extended security, further accessories, etc.: see catalog.

Note: Pump connections: Bore shape Y (60°) according to DIN 3863, pipework/flexible tempering hoses: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

Output data valid for: Room temperature 20°C, cooling water inlet 15°C and 1 bar differential pressure between cooling water inlet and - outlet. This temperature control unit has been designed to operate with cooling water up to 20°C. As the cooling water temperature increases, drop in the cooling power should be expected, and also an increased cooling water flow rate possible. Materials used in the cooling water circuit include: copper, Stainless steel 1.4401, MS, PA, PPE, PTFE and EPDM. Please use suitable cooling water.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)