

## Technical data

Operating temperature range	-45...220 °C	
Operating temperature	20 °C	
Material	brass, chromed	<b>Order-No.: 10787</b>
Sealing material	FKM	
Nennweite	12 mm	
Outside diameter	40 mm	
Length	77 mm	
Net weight	0,3 kg	
Connection	M16x1 male	
Location	Temperature control unit, application	
Max. pressure at 20°C	25 bar	
Leakage rate *	6 ml per decoupling cycle	
Cv value *	3,28	

1.0/18

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

### Optional accessories:

Verschlusskupplung #10786, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Bore shape Y (60°) to DIN 3863, piping/temperature hoses: Connectors to DIN 3863

\* Measured with water (20° C) at an ambient temperature of 20° C.