

## Technical data

Operating temperature range	-45...220 °C	
Operating temperature	20 °C	
Material	brass, chromed	<b>Order-No.: 10788</b>
Sealing material	FKM	
Nennweite	12 mm	
Outside diameter	40 mm	
Length	77 mm	
Net weight	0,42 kg	
Connection	M24X1,5 AG	
Location	hose side	
Max. pressure at 20°C	25 bar	
Leakage rate *	6 ml per decoupling cycle	
Cv value *	3,28	

**1.0/18**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

### Optional accessories:

Verschlussnippel #10789, Druckentlastungseinrichtung #10539, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Bore shape Y (60°) to DIN 3863, piping/temperature hoses: Connectors to DIN 3863

\* Measured with water (20° C) at an ambient temperature of 20° C.