

## Technical data

|                             |                           |                         |
|-----------------------------|---------------------------|-------------------------|
| Operating temperature range | -45...220 °C              |                         |
| Operating temperature       | 20 °C                     |                         |
| Material                    | brass, chromed            | <b>Order-No.: 10788</b> |
| Sealing material            | FKM                       |                         |
| Nennweite                   | 12 mm                     |                         |
| Outside diameter            | 40 mm                     |                         |
| Length                      | 77 mm                     |                         |
| Net weight                  | 0,42 kg                   |                         |
| Connection                  | M24X1,5 AG                |                         |
| Location                    | hose side                 |                         |
| Max. pressure at 20°C       | 25 bar                    |                         |
| Leakage rate *              | 6 ml per decoupling cycle |                         |
| Cv value *                  | 3,28                      |                         |

**1.0/18**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

### Optional accessories:

Verschlussnippel #10789, Druckentlastungseinrichtung #10539, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Bore shape Y (60°) to DIN 3863, piping/temperature hoses: Connectors to DIN 3863

\* Measured with water (20° C) at an ambient temperature of 20° C.