

## Technical data

Operating temperature range	-40...140 °C	
Material	stainless steel, 1.4404	
Braiding	Yes	<b>Order-No.: 10812</b>
Label*	Yes	
Nominal width (DN)	19 mm	
Length	300 cm	
Net weight	2 kg	
Connection	G3/4	
Outer covering	mit Isolation	
Max. pressure at 20°C	10 bar	
Test pressure	1,25 bar	
Min. bending radius	210 mm	
Fire rating	UL94-HB	

1.0/19

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Insulation: Special insulation with silicon cover, ends secured and covered with silicon caps.

Note: sleeve nut made of nickel-plated brass.

\*Label: stamp on band: Order No., -40°C...140°C, PS 10 bar, KW/year