

Technical data

| | | |
|-----------------------------|-------------------------|-------------------------|
| Operating temperature range | -40...140 °C | |
| Material | stainless steel, 1.4404 | |
| Braiding | Yes | Order-No.: 10819 |
| Label* | Yes | |
| Nominal width (DN) | 32 mm | |
| Length | 200 cm | |
| Net weight | 3 kg | |
| Connection | G1 1/4 | |
| Max. pressure at 20°C | 10 bar | |
| Test pressure | 1,25 bar | |
| Min. bending radius | 250 mm | |
| Fire rating | UL94-HB | |

1.0/19

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Insulation: Special insulation with silicon cover, ends secured and covered with silicon caps.

Note: sleeve nut made of nickel-plated brass.

*Label: stamp on band: Order No., -40° C...140° C, PS 10 bar, KW/year