

## Technical data

|                             |                                     |                         |
|-----------------------------|-------------------------------------|-------------------------|
| Operating temperature range | -90...200 °C                        |                         |
| Material                    | stainless steel, 1.4404             |                         |
| Braiding                    | Yes                                 | <b>Order-No.: 10867</b> |
| Label*                      | Yes                                 |                         |
| Nominal width (DN)          | 40 mm                               |                         |
| Length                      | 100 cm                              |                         |
| Net weight                  | 9,4 kg                              |                         |
| Connection 1                | Flange EN1092-1 type 11             |                         |
| Connection 2                | Flange EN1092-1 type 02,<br>type 33 |                         |
| Max. pressure at 20°C       | 10 bar                              |                         |
| Test pressure               | 1,25 bar                            |                         |
| Min. bending radius         | 260 mm                              |                         |
| Fire rating                 | UL94-HB                             |                         |

1.0/19

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

### Included Accessories:

mounting kit with 8x bolts, nuts and spring washers, as well as 2 pieces of graphite seals

Insulation: Special insulation with additional smooth silicon hose, ends covered with silicon caps.

\*Label: stamp on band: Order No., -90°C...200°C, PS 10 bar, KW/year