

Technical data

| | | |
|-----------------------------|-------------------------------------|-------------------------|
| Operating temperature range | -90...200 °C | |
| Material | stainless steel, 1.4404 | |
| Braiding | Yes | Order-No.: 10871 |
| Label* | Yes | |
| Nominal width (DN) | 50 mm | |
| Length | 100 cm | |
| Connection 1 | Flange EN1092-1 type 11 | |
| Connection 2 | Flange EN1092-1 type 02, type 33 | |
| Max. pressure at 20°C | 10 bar | |
| Test pressure | 1,25 bar | |
| Min. bending radius | 370 mm | |
| Fire rating | UL94-HB | |

1.0/19

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

mounting kit with 8x bolts, nuts and spring washers, as well as 2 pieces of graphite seals

Insulation: Special insulation with additional smooth silicon hose, ends covered with silicon caps.

*Label: stamp on band: Order No., -90°C...200°C, PS 10 bar, KW/year