

## Technical data

Operating temperature range	-90...200 °C	
Material	stainless steel, 1.4404	
Braiding	Yes	<b>Order-No.: 10874</b>
Label*	Yes	
Nominal width (DN)	50 mm	
Length	300 cm	
Connection 1	Flange EN1092-1 type 11	
Connection 2	Flange EN1092-1 type 02, type 33	
Max. pressure at 20°C	10 bar	
Test pressure	1,25 bar	
Min. bending radius	370 mm	
Fire rating	UL94-HB	

1.0/19

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

### Included Accessories:

mounting kit with 8x bolts, nuts and spring washers, as well as 2 pieces of graphite seals

Insulation: Special insulation with additional smooth silicon hose, ends covered with silicon caps.

\*Label: stamp on band: Order No., -90°C...200°C, PS 10 bar, KW/year