

The Cooling Bath are water baths with air-cooled refrigerating unit. Housing and tank of stainless steel. The refrigerating unit works continuously.

Together with the immersion thermostats can the cooling baths be used up to 200°C.

### Technical data according to DIN 12876

Operating temperature range	-20...200 °C
Cooling power	
at 20°C	0,25 kW
at 0°C	0,2 kW
at -10°C	0,12 kW
at -20°C	0,05 kW
Refrigeration machine	air-cooled, natural refrigerant
Kältemittel (ASHRAE, GSH)	R-290 (A3, H220)
Refrigerant quantity	0,041 kg
Gas warning sensor	without
Bath volume	15 l
Width bath opening WxD/ bath depth	290x316/ 200 mm
Overall dimensions WxDxH **	350x560x263 mm
Net weight	20 kg
Power supply requirement	220-240V 1~/2~ 50/60Hz
max. current	1,5 A
min. Fuse	10A
max. Fuse	16A
min. ambient temperature	5 °C
max. ambient temperature	40 °C



**Order-No.: 2010.0026.00**

**from Serial-No.: 415487 1.1/20**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

Drain valve with cap #6839, adjustable base #40763, trolley, test tube racks Typ 1-4, Bath covers in various versions: see catalogue.

Output data valid for: Room temperature 20°C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)