

Immersion Cooler with air-cooled refrigerating unit. Housing of stainless steel with 2 handles, condensing probe of stainless steel, flexible cooling connection line in special single-tube construction, protective hose with smooth surface. The refrigeration unit works continuously.

Technical data according to DIN 12876

Operating temperature range	-45...100 °C
Cooling power	.
at 0°C	0,24 kW
at -20°C	0,18 kW
at -30°C	0,1 kW
at -40°C	0,05 kW
Safety classification	I / NFL
Refrigeration machine	air-cooled, natural refrigerant
Refrigerant (ASHRAE, GHS)	R-290 (A3, H220)
Global Warming Potential (GWP)	0,02
Refrigerant quantity	0,041 kg
Gas warning sensor	without
Nominal diameter probe	48 mm
Length of probe	105 mm
Length flexible connection	1050 mm
Overall dimensions WxDxH **	190x295x360 mm
Net weight	16 kg
Power supply requirement	208-240V 1~/2~ 50/60Hz
max. current	1,4 A
min. Fuse	10A
max. Fuse	16A
Pressure equipment category	Art. 4.3 PED
min. ambient temperature	5 °C
max. ambient temperature	40 °C



Order-No.: 3003.0043.00

from Serial-No.: 394777 1.0/20

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Output data valid for: Room temperature 20°C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

** Please respect space requirements. See operating conditions at www.huber-online.com