

Chiller with air-cooled refrigerating unit and circulation pump (stainless steel). Housing, atmospheric open expansion tank and copper soldered evaporator made of stainless steel. With digital level indicator. For externally closed applications. With adjustable overtemperature protection according to DIN 12876.

Unichiller „P“ Models: Circulating pumps with a high discharge pressure for applications with high pressure drops.

#### Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

4-year warranty - registration required.

#### Technical data according to DIN 12876

Operating temperature range	-20...100 °C
temperature set point / display	5,7" colour Touchscreen
Internal temperature sensor	Pt100
Sensor external connection	Pt100
Temperature stability at -10°C	0,2 K
Interface digital	Ethernet, USB (Host u. Device), RS232
Safety classification	III / FL
Heating power	2 kW
Cooling power at ambient temperature +20°C	.
at 100°C	7,5 kW
at 20°C	7,5 kW
at 0°C	5,3 kW
at -10°C	3,3 kW
at -20°C	1,8 kW
Refrigeration machine	air-cooled, CFC- and HCFC-free
Refrigerant (ASHRAE, GHS)	R-449A (A1, H280)
Global Warming Potential (GWP)	1397
Refrigerant quantity	1,03 kg
Circulation pump:	E2
max. delivery	130 l/min
max. delivery pressure	5,7 bar
Delivery at 2,4 bar	116 l/min
Delivery at 2,5 bar	115 l/min
Delivery at 3,0 bar	108 l/min
Delivery at 3,5 bar	100 l/min
Delivery at 4,0 bar	92 l/min
Delivery at 4,5 bar	80 l/min
Delivery at 5,0 bar	59 l/min
Delivery at 5,5 bar	20 l/min
Pump connection	G1 1/4 male
min. filling capacity	18 l



**Order-No.: 3040.0034.01**

## Technical data according to DIN 12876

---

Volume of expansion	48 l
Overall dimensions WxDxH **	740x1160x1165 mm
Net weight	311 kg
sound pressure level +/- 4 dB(A)	61 dB(A)
Power supply (3 Phase)	400V 3~ 50Hz
max. current (3 Phase)	13,5 A
Fuse (3 phase)	3x16 A
Pressure equipment category	Art. 4.3 PED
Degree of Protection	IP20
min. ambient temperature	5 °C
max. ambient temperature	40 °C

---

**from Serial-No.:**

**522520**

**1.1/23**

---

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

mini-USB cable #54949, Hose coupling for G1 1/4 male, , cover expansion tank,

Optional accessories:

Com.G@te, POKO/ECS interface, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20° C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)