

Chiller with air-cooled refrigerating unit and circulation pump. Evaporator (cooler), tank and housing of stainless steel. Pump made of industrial plastic material. Temperature adjustment and temperature display digital. Level indicator with sight glass.

NEW: OLÉ controller:

OLÉ combines state-of-the-art technology with simple operation. Models with OLÉ controller are suitable for routine tasks in research and industry and are convincing as practice oriented basic equipment:

- * Large, bright OLED display
- * Simple operation with menu navigation
- * Simultaneous display of set point, internal temperature, Tmin and Tmax
- * USB (Device) and RS232 interfaces
- * Autostart function for power failure

Option: Pt100 sensor connection #10519 to display (not control) e.g. of the process temperature (only available factory fitted, additional charge)

4-year warranty - registration required.

Technical data according to DIN 12876

Operating temperature range	-20...40 °C
temperature set point / display	digital
Internal temperature sensor	Pt100
Resolution of display	0,1 K
Interface digital	USB (Device), RS232
Temperature stability at -10°C	Interface
Alarm message	0,5 K
Safety classification	optic, acoustic
Cooling power	I / NFL
at 15°C	1,5 kW
at 0°C	1 kW
at -10°C	0,7 kW
at -20°C	0,3 kW
Refrigeration machine	air-cooled, natural refrigerant
Refrigerant (ASHRAE, GHS)	R-290 (A3, H220)
Global Warming Potential (GWP)	0,02
Refrigerant quantity	0,16 kg
Circulation pump	Immersion pump
at 0,5 bar	21 l/min
max. delivery	29 l/min
max. delivery pressure	1 bar
Pump connection	G3/4 male
min. filling capacity	3,8 l
expansion tank	1,7 l
Overall dimensions WxDxH **	420x487x579 mm
Net weight	55 kg
sound pressure level +/- 4 dB(A)	63 dB(A)
Power supply requirement	220-240V 1~/2~ 50Hz
max. current	4,5 A
min. Fuse	10A
max. Fuse	16A
Degree of Protection	IP20
min. ambient temperature	5 °C
max. ambient temperature	40 °C



Order-No.: 3051.0065.98

from Serial-No.: 569509 1.0/24

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

cover expansion vessel #25178, hose coupling for G3/4 male,

Technical data according to DIN 12876

Optional accessories:

drain valve #6839, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20° C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Special Case: Acetone and Polyglycol: The plastic pump is not resistant against acetone and polyglycols (depending on the manufacturer).

It is recommended that water is mixed with either glysantine or ethylene glycol for freeze protection. A more resistant plastic is available on request at an additional cost.

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)

2. Three-phase devices with current consumption less than 63A --> with cable, without plug

3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

** Please respect space requirements. See operating conditions at www.huber-online.com