

Chiller with water-cooled refrigerating unit and circulation pump. Evaporator (cooler), tank and housing of stainless steel. Pump made of industrial plastic material. Digital Temperature adjustment and digital temperature display. Adjustable bypass. Level indicator with sight glass.

Unichiller „P“ Models: Circulating pumps with a high discharge pressure for applications with high pressure drops.

#### Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

4-year warranty - registration required.

#### Technical data according to DIN 12876

Operating temperature range	-10...40 °C	
temperature set point / display	5,7" colour Touchscreen	
Internal temperature sensor	Pt100	<b>Order-No.: 3052.0025.01</b>
Temperature stability at -10°C	0,5 K	
Interface digital	Ethernet, USB (Host u. Device), RS232	
Safety classification	I / NFL	
Cooling power at ambient temperature +20°C		
at 15°C	2,5 kW	
at 0°C	2 kW	
at -10°C	1,2 kW	
Refrigeration machine	water-cooled, CFC- and HCFC-free	
Refrigerant (ASHRAE, GHS)	R-449A (A1, H280)	
Global Warming Potential (GWP)	1397	
Refrigerant quantity	0,43 kg	
Circulation pump	B	
max. delivery	25 l/min	
max. delivery pressure	2,5 bar	
Delivery at 0,5 bar	21 l/min	
Delivery at 1,0 bar	17 l/min	
Delivery at 1,5 bar	11 l/min	
Delivery at 2,0 bar	6 l/min	
Pump connection	G3/4 male	
Cooling water connection	G1/2 male	
Consumption at water 15°C, flow 15°C	84 l/h	
Consumption at water 15°C, flow 0°C	84 l/h	
Consumption at water 15°C, flow -10°C	72 l/h	
min. cooling water differential pressure	3 bar	
max. cooling water pressure	6 bar	
min. filling capacity	3,8 l	
Volume of expansion	1,7 l	
Overall dimensions WxDxH **	420x487x579 mm	

## Technical data according to DIN 12876

---

Net weight	69 kg
sound pressure level +/- 4 dB(A)	60 dB(A)
Power supply requirement	220-240V 1~/2~ 50Hz
max. current	9 A
min. Fuse	10A
max. Fuse	16A
Degree of Protection	IP20
min. ambient temperature	5 °C
max. ambient temperature	40 °C

---

**from Serial-No.:**

**405220**

**1.1/20**

---

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

mini-USB cable #54949, cover expansion vessel, Hose coupling for G3/4 male, hose coupling cooling water for G1/2 male

Optional accessories:

Com.G@te, external sensor, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20°C, cooling water inlet 15°C and 3 bar differential pressure between cooling water inlet and outlet. This temperature control unit has been designed to operate with cooling water up to 20°C. As the cooling water temperature increases, drop in the cooling power should be expected, and also an increased cooling water flow rate possible. Materials used in the cooling water circuit include: copper, Stainless steel 1.4401, MS, PA, PPE, PTFE and EPDM. Please use suitable cooling water.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Special Case: Acetone and Polyglycol: The plastic pump is not resistant against acetone and polyglycols (depending on the manufacturer).

It is recommended that water is mixed with either glysantine or ethylene glycol for freeze protection. A more resistant plastic is available on request at an additional cost.

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)