

**Technical data**

Operating temperature range	-100...350 °C
Material	stainless steel, 1.4404
Braiding	Yes
Label*	Yes
Nominal width (DN)	20 mm
Length	50 cm
Net weight	1,26 kg
Connection	M30x1,5
Outside diameter	56 mm
Max. pressure at 20°C	6 bar
Test pressure	1,25 bar
Min. bending radius	220 mm
Fire rating	UL94-HB

**Order-No.: 6488****1.0/19**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Insulation: Special insulation with silicon cover, ends secured and covered with silicon caps.

Note: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

\*Label: stamp on band: Order No., -100°C...350°C, PS 6 bar, KW/year