

Technical data

| | |
|-----------------------------|-------------------------|
| Operating temperature range | -120...400 °C |
| Material | stainless steel, 1.4404 |
| Braiding | no |
| Nominal width (DN) | 12 mm |
| Length | 150 cm |
| Net weight | 3,6 kg |
| Connection | M24x1,5 female |
| Outside diameter | 56 mm |
| Max. pressure at 20°C | 6 bar |
| Test pressure | 1,25 bar |
| Min. bending radius | 220 mm |
| Fire rating | UL94-HB |

**Order-No.: 6785****1.0/15**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Insulation: Special insulation with silicon cover, ends secured and covered with silicon caps.

Note: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.