

**Technical data**

Operating temperature range	-100...350 °C
Material	stainless steel, 1.4404
Braiding	no
Nominal width (DN)	12 mm
Length	300 cm
Net weight	3,5 kg
Connection	M24x1,5 female
Outside diameter	44 mm
Max. pressure at 20°C	6 bar
Test pressure	1,25 bar
Min. bending radius	190 mm
Fire rating	UL94-HB

**Order-No.: 9277****1.0/15**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Insulation: Special insulation with silicon cover, ends secured and covered with silicon caps.

Note: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.