

**Technical data**

|                             |                         |
|-----------------------------|-------------------------|
| Operating temperature range | -50...200 °C            |
| Material                    | stainless steel, 1.4404 |
| Braiding                    | no                      |
| Label*                      | Yes                     |
| Nominal width (DN)          | 12 mm                   |
| Length                      | 150 cm                  |
| Net weight                  | 0,98 kg                 |
| Connection                  | M16x1                   |
| Outside diameter            | 33 mm                   |
| Max. pressure at 20°C       | 6 bar                   |
| Test pressure               | 1,25 bar                |
| Min. bending radius         | 120 mm                  |
| Fire rating                 | UL94-HB                 |

**Order-No.: 9609****1.0/15**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Insulation: Special insulation with silicon cover, ends secured and covered with silicon caps.

Note: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

\*Label: stamp on band: Order No., -50 °C...200 °C, PS 6 bar, KW/year