

Technical data

| | |
|-----------------------------|-------------------------------------|
| Operating temperature range | -60...260 °C |
| Material | industrial plastic material hose |
| Braiding | Yes |
| Label* | Yes |
| Nominal width (DN) | 25 mm |
| Length | 100 cm |
| Net weight | 2,6 kg |
| Connection | M38x1,5 |
| Outer covering | mit Isolation |
| Outside diameter | 56 mm |
| Max. pressure at 20°C | 6 bar |
| Test pressure | 1,25 bar |
| Min. bending radius | 220 mm |
| Fire rating | UL94-HB |

**Order-No.: 9616****1.0/15**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Insulation: Special insulation with silicon cover, ends secured and covered with silicon caps.

Note: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

*Label: stamp on band: Order No., -60°C...260°C, PS 6 bar, KW/year