

**Technical data**

Operating temperature range	-60...260 °C
Material	industrial plastic material hose
Braiding	Yes
Label*	Yes
Nominal width (DN)	25 mm
Length	150 cm
Net weight	2,2 kg
Connection	M38x1,5
Outside diameter	56 mm
Max. pressure at 20°C	6 bar
Test pressure	1,25 bar
Min. bending radius	220 mm
Fire rating	UL94-HB

**Order-No.: 9617****1.0/15**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Insulation: Special insulation with silicon cover, ends secured and covered with silicon caps.

Note: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

\*Label: stamp on band: Order No., -60°C...260°C, PS 6 bar, KW/year